



SurgicPro⁺

The right choice for all professionals



- Powerful torque (up to 80Ncm)
- Wide speed range (200 to 40,000min⁻¹)
- High torque accuracy
- Lightest and smallest micromotor
- LED illumination (over 32,000LUX)
- Excellent durability
- Autoclavable, thermo-disinfectable and maintenance free brushless design



Easy to Disassemble Without Tool

The DSG20L contra-angle can be disassembled with a simple twist for easy internal cleaning. However, when attached to a motor, it will not disassemble accidentally due to NSK's unique locking mechanism.




Clear Evolution

LED illumination helps the clinicians to focus more easily on the treatment area and contributes to precise surgery




Foot Control Stay in control

The Foot Control is user friendly and allows operation of all functions within the preset parameters without touching the control panel to avoid accidental activation of the micromotor outside the preset limits.



High Torque Accuracy

Advanced Hanpice Calibration(AHC) guarantees extremely accurate speed and torque for maximum safety during operation.



With Data Storage Facility

The data storage facility can record the following: data, speed, rotational direction, torque, gear ratio, irrigation solution flow setting. The total recording time is up to 100min and every recording captures data, time and duration of operation.



Data Accessibility

Treatment data can be accessed and downloaded using a USB memory stick.
*USB memory stick isn't included.

NSK Asia www.nsk-inc.com
TEL : +65-6376-5018



Powerful Partners[®]